


HANDSÄGEN & KLINGEN HAND SAWS & BLADES

JAPAN PULL™ R-SAW



					Material-Anwendung Material Suitability Index					
①	MG300FB/-EEU JAPANESE-STYLE TEMPERING MICROWAVE IMPULSE HARDENED TOOTH DAGURO-COAT BLADE	Standard-Schnitt Standard Cut	2.15mm	13 TPI	0.7mm (1.15mm)	★	★★	★★★	★★	
②	GNB300 JAPANESE-STYLE TEMPERING MICROWAVE IMPULSE HARDENED TOOTH	Standard-Schnitt Standard Cut	2.15mm	13 TPI	0.7mm (1.15mm)	★	★★	★★★	★★	
③	GNB265 JAPANESE-STYLE TEMPERING MICROWAVE IMPULSE HARDENED TOOTH	Fein-Schnitt Fine Cut	1.75mm	16 TPI	0.6mm (0.9mm)	★★	★★★	★★	★	
④	GNB265ST JAPANESE-STYLE TEMPERING MICROWAVE IMPULSE HARDENED TOOTH	Fein-Schnitt Fine Cut	1.75mm	16 TPI	0.6mm (0.9mm)	★★	★★★	★★	★	
⑤	GNB250 JAPANESE-STYLE TEMPERING MICROWAVE IMPULSE HARDENED TOOTH	Extra-Fein-Schnitt Extra Fine Cut	1.40mm	19 TPI	0.5mm (0.7mm)	★★★	★★	★		
⑥	GNB230 JAPANESE-STYLE TEMPERING MICROWAVE IMPULSE HARDENED TOOTH	Extra-Fein-Schnitt Micro Fine Cut	1.20mm	21 TPI	0.4mm (0.55mm)	★★★	★★	★		

★ Exzellent ★★ Ideal ★ Gut
★★ Best ★★ Better ★ Good